

# Combination Systems Sizing Guide

## EVP.1.2.3

### EVP 1-2-3

#### EV9347-20 Everpure High Flow CSR Plus-XC<sup>2</sup>



System available with low pressure alarm (EV9347-21)

Micro-Pure® II †

##### System

- EV9347-20 CSR Plus-XC<sup>2</sup>

##### Requirements & Specifications

- Micro-Pure® II media with anti-microbial protection inhibits potential bacterial growth
- High capacity, high volume system with XC cartridges
- Surge tank provides reserve of filtered water for peak usage
- Supports 2 carbonators, 1200 Series ice maker, 3-4 carbonators, and high volume coffee equipment
- XC cartridges provide 40% more life than MC's
- Up to 6.7 GPM flow rates

##### Replacement Cartridges

- EV9534-26 Prefilter (1 ea)
- EV9613-10 XC<sup>2</sup> (4 ea)
- EV9799-32 SS-IMF (1 ea)

#### EV9329-44 Everpure High Flow CSR Quad 4FC System



##### System

- EV9329-44 CSR Quad 4FC

##### Requirements & Specifications

- Extended-life 4FC cartridge features balanced chemical and mechanical reduction for optimum performance in varying water qualities.
- Proprietary, new and improved Fibredyne™ media inhibits potential bacterial growth.
- Built-in prefilter removes sediment and prolongs FC Cartridge life.
- Built-in shut-off valve, inlet and outlet gauges and flushing valve.
- Flow rate up to 10.0 GPM.
- Supports 3 carbonators, 1201-1500 lbs total daily ice production, and up to 4 coffee/tea brewers and 2 urns.

##### Replacement Cartridges

- EV9534-12 ECI 10 Prefilter (1 ea)
- EV9692-21 4FC (4 ea)
- EV9799-42 SS-XL (1 ea)

These sizing recommendations are merely general guidelines. For exact sizing by Manufacturer and model number, please contact Everpure Technical Service: [servicespecialist@pentair.com](mailto:servicespecialist@pentair.com) or 800.942.1153.

MicroPure II – A precoat filter with AgION antimicrobial compound that inhibits the growth of bacteria. As water passes through the filter, the carbon adsorbs chlorine, off-tastes and odors, and AgION works to inhibit any bacterial growth.